

Solutions for Electronic Specialty Markets (ESM)

Product Catalog for Electronic Specialty Markets

- 3M Electronic Specialty Markets New Product Releases
- 3M Abrasives
- 3M Adhesives, Cleaners & Compounds
- 3M Breadboards & Test Clips
- 3M Cable & Assemblies
- 3M Copper Interconnects
- 3M Fiber Optics
- 3M Fire Protection
- 3M Heat Shrink
- 3M Identification Systems
- 3M Occupational Health & Safety Products
- 3M Protective Bumpers
- 3M Reclosable Fasteners
- 3M Splicing, Terminating & Ducting
- 3M Static Control
- 3M Tapes
- 3M Terminals, Kits & Tools**
- 3M Vacuums & Accessories
- 3M Warehousing & Packaging Supplies
- 3M Wire Connectors

Other Tools

- What's New
- Sales Contacts
- U.S. Distributors

Search This Product Catalog

By Keyword

[Product Catalog for Electronic Specialty Markets](#) [3M Terminals, Kits & Tools](#) [Forks](#)  
[Highland Standard Fork Terminals - Non-Insulated Butted Seam](#)

## 3M Highland Standard Forks Non Insulated F14-10L, 16-14 AWG, 50 per bag, Obsolete

[Printer-friendly format](#)

This standard fork accepts a 16 - 14 AWG, and has case quantities of 10 bags.

3M Id : 80 - 6105 - 5586 - 6  
 GTIN(UPC/EAN) : 0 00 54007 70273 3

Additional Information

Fork terminals allow rapid connection of wire, and are usually used on free standing studs due to their wider tongues.

Learn More . . .

- [Packaging Data](#)
- [Highland Standard Forks - Non - Insulated - Product Selection Guide \(PDF 8.0 K\)](#)
- [Highland Terminals F10 - 8 thru F14 - 10 - Data Sheet \(PDF 18.7 K\)](#)
- [Terminal Stud Size Chart - Product Selection Guide \(PDF 5.2 K\)](#)

**Please Note:**

Adobe® Acrobat® Reader is required to view PDF documents.

Characteristics

Agency Approvals	UL and CSA
Barrel Style	Butted
Conductor Sizes	14 - 16 AWG
CSA File Number	LR22190
Insulation Material	Non-Insulated
Stud Size	10 American Wire Gauge (AWG)
Terminal Style	Standard
Terminal Type	Fork
UL File Number	E23438
Wire Gauge Range	14 to 16 American Wire Gauge (AWG)