

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0151330600
Status: Active
Overview: Pico-Clasp Wire-to-Board Connectors
Description: Pico-Clasp-to-Pico-Clasp Off-the-Shelf (OTS) Cable Assembly, Single Row, 50.00mm Length, 6 Circuits, White

Documents:
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable Assemblies
Series 15133
Application Signal, Wire-to-Board
Assembly Configuration Dual Ended Connectors
Connector to Connector Pico-Clasp-to-Pico-Clasp
Overmolded No
Overview Pico-Clasp Wire-to-Board Connectors
Product Literature Order No 987651-6143
Product Name Pico-Clasp
Type Discrete Wire Assembly
UPC 191128139267

Physical
Cable Length 50.00mm
Circuits (Loaded) 6
Color - Resin White
Gender Female-Female
Lock to Mating Part Yes
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 0.622/g
Number of Rows 1
Packaging Type Bag
Pitch - Mating Interface 1.00mm
Plating min - Mating 1.000µm
Plating min - Termination 1.000µm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 0.60mm
Wire Size AWG 28
Wire/Cable Type UL 1571

Electrical
Current - Maximum per Contact 1.0A
Voltage - Maximum 50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers
Sales Drawing 2012341666-000



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
ED/71/2019 (16 July
2019)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
15133 Series

Mates With
501940 , 203560 , 203561 Vertical PCB
Header
 501953 , 203562 , 203563
Right Angle PCB Header