

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0152660556](#)  
**Status:** **Active**  
**Overview:** Premo-Flex Cable Jumpers  
**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 50 Circuits, 0.305m Cable Length, Tin (Sn) Plating

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-15266-001-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Packaging Specification PK-15266-001-001 (PDF)</a>	

**General**

Product Family	Cable
Series	<a href="#">15266</a>
Comments	Contacts on opposite sides, Type D, Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	<a href="#">Premo-Flex Cable Jumpers</a>
Product Literature Order No	987650-6631
Product Name	Premo-Flex FFC Jumper
UPC	884982431874

**Physical**

Cable Length	0.305m
Circuits (Loaded)	50
Circuits (maximum)	50
Net Weight	4.862/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-15266-001-001
Product Specification	PS-15266-001-001
Sales Drawing	SD-15266-001



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
------------	--------------

ELV	Not Reviewed
-----	--------------

RoHS Phthalates	Not Reviewed
-----------------	--------------

**Search Parts in this Series**

[15266 Series](#)

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[541045033](#) , [541325033](#) , [5019515000](#)