

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0314022200](#)
Status: **Active**
Overview: [MX64 Sealed Connectors](#)
Description: 2.54mm MX64 Sealed Single Row Crimp Housing, GET Terminal, Gray, 2 Circuits, Key B, without CPA Lock

Documents:

3D Model	Application Specification AS-31402-000-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31300-256-001 (PDF)
Drawing (PDF)	Test Summary TS-31402-001-1X2-001 (PDF)
Product Specification PS-31402-000-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Housings
Series	31402
Application	Power, Wire-to-Board
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership
Overview	MX64 Sealed Connectors
Polarization	B
Product Name	MX64
UPC	822348232680

Physical

Circuits (maximum)	2
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	4.341/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-31402-000-001
Packaging Specification	PK-31300-256-001
Product Specification	PS-31402-000-001
Sales Drawing	SD-31402-211-001
Test Summary	TS-31402-001-1X2-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[31402 Series](#)

Mates With

Sensors, Other USCAR Interfaces

Use With

Molex GET Terminals [34230](#)