

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0340620032](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: [MX150 Cable-Sealed Female Connector Assembly, Single Row, 2 Circuits, Keying Option B, with Clipslot, Gray](#)

Documents:

3D Model	Packaging Specification PK-30907-879-001 (PDF)
Drawing (PDF)	Test Summary TS-34062-992-001 (PDF)
Product Specification PS-34062-000-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34062-000-001 (PDF)	



Series image - Reference only

General

Product Family	Crimp Housings
Series	34062
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA), No Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	883906212001

Physical

Circuits (maximum)	2
Color - Resin	Gray (Light)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.257/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34062-000-001
Packaging Specification	PK-30907-879-001
Product Specification	PS-34062-000-001
Sales Drawing	SD-34062-002-000, SD-34062-004-001
Test Summary	TS-34062-992-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34062](#) Series

Mates With

[MX150 Cable-Sealed Male Connector 34675](#)

Use With

[Tin \(Sn\) Cable Seal Female Terminal 34083](#)

[Silver \(Ag\) and Gold \(Au\) Cable Seal Female Terminal 34081](#)