


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348978160](#)
Status: **Active**
Overview: [Mini50 Connection Systems](#)
Description: Mini50 Unsealed Header, Right-Angle, SMT, Dual Row, 16 Circuits, Tin (Sn) Plating, Polarization Option A, Black, Tape and Reel

Documents:

3D Model	Product Specification PS-34791-020-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	Product Literature (PDF)



General

Product Family	PCB Headers
Series	34897
Application	Automotive, Power, Signal, Wire-to-Board
Overview	Mini50 Connection Systems
Product Name	Mini50
UPC	887191459271

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	SPS
Net Weight	3.072/g
Number of Rows	2
Orientation	Right Angle
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V DC

Material Info

Reference - Drawing Numbers

Product Specification	PS-34791-020-001
Sales Drawing	SD-34897-001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34897 Series](#)

Mates With

[34824 Mini50 Unsealed Dual Row Receptacle](#)