

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0386007820](#)  
**Status:** **Active**  
**Overview:** [Beau Barrier Strips](#)  
**Description:** 6.35mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, with Clamp Washer Screws, 300V, 20 Circuits

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

Product Family	Terminal Blocks
Series	<a href="#">38600</a>
Application	N/A
Component Type	One Piece
Overview	<a href="#">Beau Barrier Strips</a>
Product Name	Fixed Mount Barrier
Type	Barrier Strip
UPC	800756248028

**Physical**

Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Number of Rows	1
Orientation	Horizontal
PC Tail Length	5.10mm
PCB Thickness - Recommended	3.18mm
Panel Mount	No
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm
Polarized to Mating Part	No
Shrouded	Tri-Barrier
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +130°C
Wire Size AWG	18, 20, 22

**Electrical**

Current - Maximum per Contact	10.0A
Voltage - Maximum	300V

**Solder Process Data**


Lead-freeProcess Capability	WAVE
-----------------------------	------

**Material Info**

Engineering Number	60520-C-50
--------------------	------------

**Reference - Drawing Numbers**

Sales Drawing	SD-38600-001
---------------	--------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[38600 Series](#)

This document was generated on 09/20/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**