

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0533533071

Status:


Active

Overview:

SlimStack Board-to-Board Connectors

Description:

SlimStack Board-to-Board Connector, 0.80mm Pitch, Floating Series, Plug, 7.00 or 8.00mm Mated Height, 30 Circuits, Vertical, without Boss



Series image - Reference only

- Documents:
- 3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-52465-010-001 (PDF)

Product Specification PS-52588-032-001 (PDF)

Datasheet (PDF)

Product Guide (PDF)

RoHS Certificate of Compliance (PDF)

Reference Guide (PDF)

General	
Product Family	PCB Headers
Series	53353
Application	Board-to-Board, Signal
Overview	SlimStack Board-to-Board Connectors
Product Name	SlimStack
Series Name	0.80 Floating
UPC	822348795406
Physical	
Breakaway	No
Circuits (Loaded)	30
Circuits (maximum)	30
Durability (mating cycles max)	30
Glow-Wire Capable	No
Lock to Mating Part	None
Mated Height	7.00mm, 8.00mm
Mated Width	5.10mm, 7.20mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	779.100/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.80mm
Polarized to PCB	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-52465-010-001, PS-52588-032-001
Sales Drawing	SD-53353-003, SD-53353-004

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

53353 Series

Mates With

52465 , 52588 PCB Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION