

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0565790511](#)
Status: **Obsolete**
Description: USB On-The-Go (OTG) Mini-AB Receptacle, Right Angle, Through Hole Solder Tails and Shell Tabs
Replacement Part Number: [565790519](#)

Documents:
[Drawing \(PDF\)](#)

General

Product Family	I/O Connectors
Series	56579
Application	Wire-to-Board
Component Type	Receptacle
Product Name	USB
Replacement Part Number	565790519
Type	Mini-AB (OTG)

Physical

Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Gray
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Material - Resin	High Temperature Thermoplastic
Orientation	Right Angle
PC Tail Length	1.80mm (.071")
PCB Retention	Yes
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm (.031")
Pitch - Termination Interface	0.80mm (.031")
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	4.064µm (160µ")
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	0°C to +50°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-56579-001
Product Specification	PS-56579-014

EU RoHS
Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[56579Series](#)

Mates With

USB OTG mini-A plug|USB OTG mini-B plug

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION