

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934442101](#)
Status: **Active**
Overview: [ML-XT Sealed Connection System](#)
Description: ML-XT Sealed 3 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Black

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
 Series [93444](#)
 Application Power, Signal, Wire-to-Wire
 Overview [ML-XT Sealed Connection System](#)
 Product Literature Order No 987651-0201
 Product Name ML-XT
 UPC 889056190015

Physical

Circuits (maximum) 3
 Color - Resin Black
 Gender Receptacle
 Glow-Wire Capable No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Resin Nylon
 Net Weight 6.892/g
 Number of Rows 2
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface N/A
 Polarized to Mating Part Yes
 Temperature Range - Operating -55° to +125°C

Electrical

Current - Maximum per Contact 13.0A

Material Info

Reference - Drawing Numbers

Sales Drawing 934430020-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/71/2019 (16 July
 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93444](#) Series

Mates With

ML-XT Sealed 3 Circuit Plug Housing
[934452101](#)

Use With

ML-XT Male (Pin) Terminal [845240004](#)
 (Nickel), ML-XT Male (Pin) Terminal
[845240014](#) (Selective Gold), ML-XT 3
 Circuit Receptacle Wedgelock [93447](#) , ML-
 XT Blind Cavity Plug [934941000](#)