

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0937921218](#)  
**Status:** **Active**  
**Overview:** SRC - Sealed Rectangular Connectors  
**Description:** SRC Housing, Male, Hybrid 30 Pin Mixed Power and Signal (12 x MX150 + 18 x MX150L), SPS/Nylon, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 937320001-K (PDF)</a>
<a href="#">Product Specification 850710020-K (PDF)</a>	<a href="#">Packaging Specification 937921000-K (PDF)</a>
<a href="#">Product Specification 937320001-P (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 850830010-A (PDF)</a>	<a href="#">Product Literature (PDF)</a>



**General**

Product Family	Crimp Housings
Series	<a href="#">93792</a>
Application	Power, Signal, Wire-to-Wire
Overview	<a href="#">SRC - Sealed Rectangular Connectors</a>
Product Literature Order No	987650-7391
Product Name	SRC
UPC	889056621687

**Physical**

Circuits (maximum)	30
Circuits Detail	12 x MX150™ + 18 x MX150L™
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Number of Rows	8
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	850830010-A
Packaging Specification	937320001-K, 937921000-K
Product Specification	850710020-K, 937320001-P
Sales Drawing	937921000-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**Search Parts in this Series**

[93792 Series](#)

**Mates With**

SRC Power Receptacle Housing [850841218](#)

**Use With**

MX150 Male Terminals [33000](#) . MX150L Male Terminal [19431](#)