

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0987891201](#)
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: NSCC Single Part, Unsealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Black

Documents:

Drawing (PDF)	Application Specification AS-98788-003-001 (PDF)
Application Specification 987880002-AS-CH-001 (PDF)	Application Specification AS-98788-003-FR (PDF)
Application Specification 987880003-AS-CH-001 (PDF)	Packaging Specification PK-98789-001 (PDF)
Application Specification AS-98788-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link	63812-1200
Application Tooling Part Link	63813-5700

General

Product Family	Crimp Housings
Series	98789
Application	Power, Wire-to-Wire
Overview	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822348803408

Physical

Circuits (maximum)	10
Circuits Detail	10x1.5mm female terminal
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Resin	Polyester
Net Weight	11.520/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.25mm
Pitch - Termination Interface	6.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +120°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	09211EV10F1
--------------------	-------------

Reference - Drawing Numbers

Application Specification	987880002-AS-CH-001, 987880003-AS-CH-001, AS-98788-002-001, AS-98788-003-001, AS-98788-003-FR
Packaging Specification	PK-98789-001
Sales Drawing	SD-98789-003



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[98789](#) Series

Mates With

[987881201](#) 1.50mm Pitch NSCC, Wire-to-Wire, Housing

Use With

Sicma 1.5 and 2.8mm Male Terminals for Single Wire Seal from FCI

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool for Seal Plug	638121200
Extractor Tool for CTX64 Female Crimp Terminals	638135700

This document was generated on 02/21/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION