

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192070005**
Status: **Active**
Overview: Splices
Description: NylaKrimp™ Parallel Splice for 10-12 AWG Wire

Documents:

Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-011-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	<u>19207</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<u>Splices</u>
Product Name	NylaKrimp™, Parallel
UPC	800753052994

Physical


Barrel Type	Closed - Brazed
Color - Resin	Yellow
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.119/g
Packaging Type	Bag
Wire Insulation Diameter	5.30mm max.
Wire Size AWG	10, 12

Material Info

Engineering Number	CS-N-303
--------------------	----------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	CSN303CD



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

19207 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION