

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192030050](#)
Status: **Active**
Overview: [High-Temperature Temp Terms Terminals and Splices](#)
Description: Krimptite™ Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier

Documents:

Drawing (PDF)	Product Specification PS-19902-015 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E32244

General

Product Family	Ring and Spade Terminals
Series	19203
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite™, Temp-Terms
Type	Ring
UPC	800753049727

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.683/g
Packaging Type	Adhesive Tape on Reel
Stud Size	8 (M4)
Wire Size AWG	14, 16
Wire Size mm²	1.00-2.50

Material Info

Old Part Number B-S-137-08T

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-015
Sales Drawing	SD-19203-023



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[19203 Series](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Mini-Mac™ Applicator	0638858100
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	0190270055