

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1510340014](#)
Status: **Active**
Overview: [EXTreme Guardian System](#)
Description: 11.00mm Pitch EXTreme Guardian Power Receptacle Assembly, 6 AWG, PBT, 4 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [151034](#)
 Application Power, Wire-to-Board
 Overview [EXTreme Guardian System](#)
 Product Name EXTreme Guardian
 UPC 889056225182

Physical

Circuits (maximum) 4
 Color - Resin Black
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Lock to Mating Part Yes
 Material - Resin PBT
 Net Weight 22.141/g
 Number of Rows 1
 Packaging Type Tray
 Panel Mount No
 Pitch - Mating Interface 11.00mm
 Temperature Range - Operating -40° to +105°C


Electrical

Current - Maximum per Contact 80.0A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/71/2019 (16 July
 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[151034](#) Series

Mates With

[151035](#) EXTreme Guardian Power Right-Angle PCB Header, [151053](#) EXTreme Guardian Power Vertical PCB Header

Use With

[46818](#) Power Harness Crimp Receptacle, [151076](#) TPA Clips, [46819](#) High-Power Terminals