This document was generated on 05/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1601116006

Status: Active

Overview:

Description: MX150 Hybrid Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, Keying Option A, with Connector Position Assurance, Black

EU ELV
Compliant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
160111 Series

Mates With
MX150 Hybrid Sealed Male Connector Assembly 160112

Use With
MX150 Female Terminal 33012 , 33001

Industry Standard Terminal 2.80mm

General	
Product Family	Crimp Housings
Series	160111
Application	Power, Wire-to-Wire
Comments	with Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	mx150_sealed_connector_system
Product Name	MX150
UPC	889056821681
Physical	
Circuits (maximum)	12
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	20.104/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Material Info	
Reference - Drawing Numbers	
Application Specification	1601110001-AS-000
Packaging Specification	1601118000-000, 1601118002-000, 1601119000-000
Product Specification	1601110001-PS-000
Sales Drawing	1601110000-000

This document was generated on 05/07/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION