

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190800006](#)  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** InsulKrimp™ Ring Tongue Terminal for 10-12 AWG Heavy Duty Wire, Stud Size 6, 8, 10

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-011-001 (PDF)</a>
<a href="#">Product Specification PS-19902-009-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Ring and Spade Terminals
Series	<a href="#">19080</a>
Comments	Heavy Duty
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<a href="#">Solderless Terminals</a>
Product Name	InsulKrimp™
Type	Ring
UPC	800755958577

**Physical**

Barrel Type	Closed
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Stud Size	10 (M5)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	.250mm max
Wire Size AWG	10, 12

**Material Info**

Engineering Number	C-2006-MSXT
--------------------	-------------

**Reference - Drawing Numbers**

Product Specification	PS-19902-009-001, PS-19902-011-001
Sales Drawing	MSRINGIN

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[19080 Series](#)