

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0982680940**
Status: **Active**
Overview: Premo-Flex™ Cable Jumpers
Description: 1.25mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 23 Circuits, 0.305m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-98268-001-001 \(PDF\)](#)
[Product Specification PS-98268-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	98268
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ Cable Jumpers
Product Name	Premo-Flex™ FFC Jumper
UPC	800756948621

Physical

Cable Length	0.305m
Circuits (Loaded)	23
Circuits (maximum)	23
Packaging Type	Bag
Pitch - Termination Interface	1.25mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	1.4A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98268-001-001
Product Specification	PS-98268-001-001
Sales Drawing	SD-98268-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[98268 Series](#)

Use With

Molex FFC – FPC connector. Be sure to match like plating.