


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2012010040](#)
Status: **Active**
Overview: [Spot-On Wire-to-Board Connector System](#)
Description: Spot-On Wire-to-Board Header with Nail, 2.00mm Pitch, Single Row, Vertical, 4 Circuits, Matte Tin (Sn) Plating, Natural

Documents:

| | |
|--|---|
| 3D Model | Product Specification 2011960000-A01 (PDF) |
| Drawing (PDF) | Product Specification 2012000000-PS-000 (PDF) |
| 3D Model (PDF) | Packaging Specification 2012019200-200 (PDF) |
| Product Specification 2011960000-A00 (PDF) | RoHS Certificate of Compliance (PDF) |



Series image - Reference only

General

| | |
|----------------|--|
| Product Family | PCB Headers |
| Series | 201201 |
| Application | Signal, Wire-to-Board |
| Overview | Spot-On Wire-to-Board Connector System |
| Product Name | Spot-On |
| UPC | 191128253031 |

Physical

| | |
|--------------------------------|-----------------------|
| Breakaway | No |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 30 |
| First Mate / Last Break | No |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Matte Tin |
| Material - Plating Termination | Matte Tin |
| Material - Resin | Polyamide |
| Net Weight | 1297.300/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| PCB Locator | No |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 2.00mm |
| Pitch - Termination Interface | 2.00mm |
| Plating min - Mating | 1.000µm |
| Plating min - Termination | 1.000µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Robotic Placement | Vacuum Pick-Up Area |
| Shrouded | Fully |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface: Style | Surface Mount |

Electrical

| | |
|-------------------------------|------------------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 250V AC (RMS)/DC |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[201201](#) Series

Mates With

Spot-On Receptacle Housing [201200](#)

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

2012019200-200

2011960000-A00, 2011960000-A01, 2012000000-
PS-000

2012010060-SD-000, 2012011060-SD-000

This document was generated on 01/16/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION