

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2051950360](#)  
**Status:** **Active**  
**Overview:** Easy-On FFC FPC Connectors  
**Description:** Easy-On FFC/FPC Connector, 0.50mm Pitch, FV2R Series, Plug, 70.00mm Shielded FFC, Vertical, 7.10mm Mated Height, 36 Circuits

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 2051950360-SPK (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 2051960360-PS (PDF)</a>	



**General**

Product Family	FFC/FPC Connectors
Series	<a href="#">205195</a>
Overview	<a href="#">Easy-On FFC FPC Connectors</a>
Product Name	Easy-On
Series Name	FV2R
UPC	191128792943

**Physical**

Actuator Type	Flexi-Latch
Circuits (Loaded)	36
Circuits (maximum)	36
Color - Resin	Black
Contact Position	Dual
Durability (mating cycles max)	20
Mated Height	7.10mm
Material - Resin	Polyester
Net Weight	1384.400/mg
Number of Rows	2
Orientation	Vertical
PCB Mounting	N/A
PCB Retention	N/A
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Polarized to PCB	N/A
Stackable	No
Temperature Range - Operating	-20° to +85°C
Wire/Cable Type	FFC/FPC

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	2051950360-SPK
Product Specification	2051960360-PS
Sales Drawing	2051950360-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Missing Compliance Data**

**REACH SVHC**

Missing Compliance Data

**Halogen-Free**

**Status**

**Missing Compliance Data**

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Missing Compliance Data

**Search Parts in this Series**

[205195 Series](#)

**Mates With**

Easy-On Vertical Receptacle [2051960360](#)