

THESE PART NUMBERS ARE NOT RECOMMENDED, FOR NEW APPLICATIONS USE THE TRAY PACKED PART NUMBERS

[illegible]

<u>DOCUMENT NUMBER:</u> SDA-5569-NA2*-*	<u>Drawn By:</u> JDFOX	<u>Checked By:</u> JBELL	<u>Approved By:</u> FSMITH
---	----------------------------------	------------------------------------	--------------------------------------

TRAY PACKAGED PER PK-5569-003										
PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L	PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L	
26-01-3127	5569-02A2GS2-210-T	2	15 μ" SELECT GOLD SEE NOTE 2 OPTION "GS2"	94V-0	46999-0538	5569-02A2GS2-400-T	2	15 μ" SELECT GOLD SEE NOTE 2 OPTION "GS2"	BLACK 94V-0	
26-01-3128	5569-04A2GS2-210-T	4			46999-0539	5569-04A2GS2-400-T	4			
NOT TOOLED	5569-06A2GS2-210-T	6			46999-0540	5569-06A2GS2-400-T	6			
NOT TOOLED	5569-08A2GS2-210-T	8			46999-0541	5569-08A2GS2-400-T	8			
NOT TOOLED	5569-10A2GS2-210-T	10			46999-0542	5569-10A2GS2-400-T	10			
NOT TOOLED	5569-12A2GS2-210-T	12			46999-0543	5569-12A2GS2-400-T	12			
NOT TOOLED	5569-14A2GS2-210-T	14			46999-0544	5569-14A2GS2-400-T	14			
NOT TOOLED	5569-16A2GS2-210-T	16			46999-0545	5569-16A2GS2-400-T	16			
NOT TOOLED	5569-18A2GS2-210-T	18			46999-0546	5569-18A2GS2-400-T	18			
NOT TOOLED	5569-20A2GS2-210-T	20			46999-0547	5569-20A2GS2-400-T	20			
NOT TOOLED	5569-22A2GS2-210-T	22			46999-0548	5569-22A2GS2-400-T	22			
NOT TOOLED	5569-24A2GS2-210-T	24			46999-0549	5569-24A2GS2-400-T	24			
26-01-3141	5569-02A2GS3-T	2	50 μ" SELECT GOLD SEE NOTE 2 OPTION "GS3"	94V-2			2			
26-01-3142	5569-04A2GS3-T	4					4			
26-01-3143	5569-06A2GS3-T	6					6			
26-01-3144	5569-08A2GS3-T	8					8			
NOT TOOLED	5569-10A2GS3-T	10					10			
NOT TOOLED	5569-12A2GS3-T	12					12			
NOT TOOLED	5569-14A2GS3-T	14					14			
26-01-3148	5569-16A2GS3-T	16					16			
NOT TOOLED	5569-18A2GS3-T	18					18			
NOT TOOLED	5569-20A2GS3-T	20					20			
NOT TOOLED	5569-22A2GS3-T	22					22			
NOT TOOLED	5569-24A2GS3-T	24					24			
46999-0001	5569-02A2S-BL-T	2	MATTE TIN OVER NICKEL SEE NOTE 2 OPTION "S"	BLACK 94V-2			2			
46999-0002	5569-04A2S-BL-T	4					4			
46999-0003	5569-06A2S-BL-T	6					6			
46999-0004	5569-08A2S-BL-T	8					8			
46999-0005	5569-10A2S-BL-T	10					10			
46999-0006	5569-12A2S-BL-T	12					12			
46999-0007	5569-14A2S-BL-T	14					14			
46999-0008	5569-16A2S-BL-T	16					16			
46999-0009	5569-18A2S-BL-T	18					18			
46999-0010	5569-20A2S-BL-T	20					20			
46999-0011	5569-22A2S-BL-T	22					22			
46999-0012	5569-24A2S-BL-T	24					24			
46999-0013	5569-02A2S-400-T	2	MATTE TIN OVER NICKEL SEE NOTE 2 OPTION "S"	BLACK 94V-0	46999-0515	5569-02A2G-400-T	2	30 μ" SELECT GOLD SEE NOTE 2 OPTION "G"	BLACK 94V-0	
46999-0014	5569-04A2S-400-T	4			46999-0516	5569-04A2G-400-T	4			
46999-0015	5569-06A2S-400-T	6			46999-0517	5569-06A2G-400-T	6			
46999-0016	5569-08A2S-400-T	8			46999-0518	5569-08A2G-400-T	8			
46999-0017	5569-10A2S-400-T	10			46999-0519	5569-10A2G-400-T	10			
46999-0018	5569-12A2S-400-T	12			46999-0520	5569-12A2G-400-T	12			
46999-0019	5569-14A2S-400-T	14			46999-0521	5569-14A2G-400-T	14			
46999-0020	5569-16A2S-400-T	16			46999-0522	5569-16A2G-400-T	16			
46999-0021	5569-18A2S-400-T	18			46999-0523	5569-18A2G-400-T	18			
46999-0022	5569-20A2S-400-T	20			46999-0524	5569-20A2G-400-T	20			
46999-0023	5569-22A2S-400-T	22			46999-0525	5569-22A2G-400-T	22			
46999-0024	5569-24A2S-400-T	24			46999-0526	5569-24A2G-400-T	24			
REVISION:	ECR/ECN INFORMATION:		TITLE:						SHEET No.	
M7	EC No: UCP2018-0918		MINI-FIT JR.® RIGHT ANGLE HEADER ASSEMBLIES WITH MOUNTING PEGS						- 3 -	
	DATE: 2014/08/29									
DOCUMENT NUMBER:			Drawn By:		Checked By:		Approved By:			
SDA-5569-NA2*-*			JDFOX		JBELL		FSMITH			
Filename: SPOMASTER.DOC			Revision: 1		Location: Workmanager General Docs Class.		Date: 4-15-2002			



TRAY PACKAGED PER PK-5569-003																											
PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L	PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L																		
50-36-1757	5569-02A2S-T	2	MATTE TIN OVER NICKEL SEE NOTE 2 OPTION "S"	94V-2	50-36-1758	5569-02A2S-210-T	2	MATTE TIN OVER NICKEL SEE NOTE 2 OPTION "S"	94V-0																		
50-36-1767	5569-04A2S-T	4			50-36-1768	5569-04A2S-210-T	4																				
50-36-1777	5569-06A2S-T	6			50-36-1778	5569-06A2S-210-T	6																				
50-36-1787	5569-08A2S-T	8			50-36-1788	5569-08A2S-210-T	8																				
50-36-1797	5569-10A2S-T	10			50-36-1798	5569-10A2S-210-T	10																				
50-36-1807	5569-12A2S-T	12			50-36-1808	5569-12A2S-210-T	12																				
50-36-1817	5569-14A2S-T	14			50-36-1818	5569-14A2S-210-T	14																				
50-36-1827	5569-16A2S-T	16			50-36-1828	5569-16A2S-210-T	16																				
50-36-1837	5569-18A2S-T	18			50-36-1838	5569-18A2S-210-T	18																				
50-36-1847	5569-20A2S-T	20			50-36-1848	5569-20A2S-210-T	20																				
50-36-1857	5569-22A2S-T	22																									
50-36-1867	5569-24A2S-T	24			50-36-1858	5569-22A2S-210-T	22																				
					50-36-1868	5569-24A2S-210-T	24																				
50-36-1755	5569-02A2GS-T	2	30 μ" SELECT GOLD SEE NOTE 2 OPTION "GS"	94V-2	50-36-1756	5569-02A2GS-210-T	2	30 μ" SELECT GOLD SEE NOTE 2 OPTION "GS"	94V-0																		
50-36-1765	5569-04A2GS-T	4			50-36-1766	5569-04A2GS-210-T	4																				
50-36-1775	5569-06A2GS-T	6			50-36-1776	5569-06A2GS-210-T	6																				
50-36-1785	5569-08A2GS-T	8			50-36-1786	5569-08A2GS-210-T	8																				
50-36-1795	5569-10A2GS-T	10			50-36-1796	5569-10A2GS-210-T	10																				
50-36-1805	5569-12A2GS-T	12			50-36-1806	5569-12A2GS-210-T	12																				
50-36-1815	5569-14A2GS-T	14			50-36-1816	5569-14A2GS-210-T	14																				
50-36-1825	5569-16A2GS-T	16			50-36-1826	5569-16A2GS-210-T	16																				
50-36-1835	5569-18A2GS-T	18			50-36-1836	5569-18A2GS-210-T	18																				
50-36-1845	5569-20A2GS-T	20			50-36-1846	5569-20A2GS-210-T	20																				
39-30-1221	5569-22A2GS-T	22			50-36-1856	5569-22A2GS-210-T	22																				
50-36-1865	5569-24A2GS-T	24			50-36-1866	5569-24A2GS-210-T	24																				
26-01-3177	5569-02AGS3-210-T	2	50 μ" SELECT GOLD SEE NOTE 2 OPTION "GS3"	94V-0	26-01-3101	5569-02A2GS-BL-T	2	30 μ" SELECT GOLD SEE NOTE 2 OPTION "GS"	BLACK 94V-2																		
26-01-3178	5569-04AGS3-210-T	4			NOT TOOLED	5569-04A2GS-BL-T	4																				
		6			NOT TOOLED	5569-06A2GS-BL-T	6																				
		8			NOT TOOLED	5569-08A2GS-BL-T	8																				
26-01-3094	5569-10AGS3-210-T	10			NOT TOOLED	5569-10A2GS-BL-T	10																				
		12			NOT TOOLED	5569-12A2GS-BL-T	12																				
		14			NOT TOOLED	5569-14A2GS-BL-T	14																				
		16			26-01-3108	5569-16A2GS-BL-T	16																				
		18			NOT TOOLED	5569-18A2GS-BL-T	18																				
		20			NOT TOOLED	5569-20A2GS-BL-T	20																				
		22	NOT TOOLED	5569-22A2GS-BL-T	22																						
		24			NOT TOOLED	5569-24A2GS-BL-T	24																				
26-01-3114	5569-02A2GS2-T	2	15 μ" SELECT GOLD SEE NOTE 2 OPTION "GS2"	94V-2																							
26-01-3115	5569-04A2GS2-T	4																									
26-01-3116	5569-06A2GS2-T	6																									
NOT TOOLED	5569-08A2GS2-T	8																									
NOT TOOLED	5569-10A2GS2-T	10																									
26-01-3119	5569-12A2GS2-T	12																									
NOT TOOLED	5569-14A2GS2-T	14																									
NOT TOOLED	5569-16A2GS2-T	16																									
NOT TOOLED	5569-18A2GS2-T	18																									
NOT TOOLED	5569-20A2GS2-T	20																									
NOT TOOLED	5569-22A2GS2-T	22																									
26-01-3126	5569-24A2GS2-T	24																									
<table border="1"> <tr> <td> REVISION: M7 </td> <td> ECR/ECN INFORMATION: EC No: UCP2018-0918 DATE: 2014/08/29 </td> <td colspan="5"> TITLE: MINI-FIT JR.® RIGHT ANGLE HEADER ASSEMBLIES WITH MOUNTING PEGS </td> <td colspan="2"> SHEET No. - 4 - </td> </tr> <tr> <td colspan="2"> DOCUMENT NUMBER: SDA-5569-NA2*-* </td> <td colspan="2"> Drawn By: JDFOX </td> <td colspan="2"> Checked By: JBELL </td> <td colspan="3"> Approved By: FSMITH </td> </tr> </table>										REVISION: M7	ECR/ECN INFORMATION: EC No: UCP2018-0918 DATE: 2014/08/29	TITLE: MINI-FIT JR.® RIGHT ANGLE HEADER ASSEMBLIES WITH MOUNTING PEGS					SHEET No. - 4 -		DOCUMENT NUMBER: SDA-5569-NA2*-*		Drawn By: JDFOX		Checked By: JBELL		Approved By: FSMITH		
REVISION: M7	ECR/ECN INFORMATION: EC No: UCP2018-0918 DATE: 2014/08/29	TITLE: MINI-FIT JR.® RIGHT ANGLE HEADER ASSEMBLIES WITH MOUNTING PEGS					SHEET No. - 4 -																				
DOCUMENT NUMBER: SDA-5569-NA2*-*		Drawn By: JDFOX		Checked By: JBELL		Approved By: FSMITH																					
File name: SPOMASTER.DOC Revision: 1 Location: Workmanager General Docs Class. Date: 4-15-2002																											

(SEE NOTE 4.)


DIMENSIONS TYPICAL FOR
ALL CIRCUITS SIZES



12 CORNER CORE-OUTS ARE OPTIONAL AND MAY OR MAY NOT BE PRESENT.



RECOMMENDED HOLE LAYOUT FOR
.070/(1.78) MAX. THICK P.C. BOARD
VIEWED FROM COMPONENT SIDE



© THIRD ANGL
PROJECTION

molex

SHEET NO.

SDA-5569-NA2*-*

1 OF 1

SIZE	
------	--

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

E
TH

SHEE
1 0
2 MC