

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2147531021](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-Fit 3.0 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 150.00mm Length, Tin (Sn) Plating, 2 Circuits, Black

Documents:

| | |
|--------------------------------|--|
| 3D Model | Datasheet (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| 3D Model (PDF) | |



Series image - Reference only

General

| | |
|------------------------|--|
| Product Family | Cable Assemblies |
| Series | 214753 |
| Application | Power, Wire-to-Wire |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Micro-Fit 3.0-to-Pigtail |
| Overmolded | No |
| Overview | Micro-Fit Connector System |
| Product Name | Micro-Fit 3.0 |
| Type | Discrete Wire Assembly |
| UPC | 193264586103 |

Physical

| | |
|--------------------------------|-------------------------|
| Cable Length | 150.00mm |
| Circuits (Loaded) | 2 |
| Color - Resin | Black |
| Gender | Male-Pigtail |
| Lock to Mating Part | Yes |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 4.319/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Pitch - Mating Interface | 3.00mm |
| Plating min - Mating | 1.016µm |
| Plating min - Termination | 1.016µm |
| Single Ended | Yes |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.85mm max. |
| Wire Size AWG | 18 |
| Wire/Cable Type | Discrete Wire, UL 10002 |

Electrical

| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 8.5A |
| Voltage - Maximum | 300V AC/DC |

Material Info

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 2147531021-000 |
|---------------|----------------|

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214753 Series](#)

Mates With

[Micro-Fit 3.0 Receptacle Housing 43645](#)