

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0015311092](#)  
**Status:** **Active**  
**Description:** 4.80mm Pitch Wire-to-Wire Receptacle Housing, 9 Circuits

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-5025-003 (PDF)</a>
<a href="#">Product Specification PS-5025-001 (PDF)</a>	<a href="#">Packaging Specification SPK-5025-001 (PDF)</a>
<a href="#">Product Specification PS-5025-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">5025</a>
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800753604179

**Physical**

Circuits (maximum)	9
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	3193.400/mg
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Temperature Range - Operating	-40°C to +105°C

**Material Info**

Engineering Number	5025-09R1
--------------------	-----------

**Reference - Drawing Numbers**

Packaging Specification	SPK-5025-001
Product Specification	PS-5025-001, PS-5025-002, PS-5025-003
Sales Drawing	SD-5025-09R1

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[5025 Series](#)

**Mates With**

[5025 Plug](#)

**Use With**

[5005](#)