
This document was generated on 07/31/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0022566087
Status: Active
Overview: SL™ Modular Connectors
Description: 2.54mm Pitch SL™ Crimp Housing, Dual Row, Version F, 8 Circuits



Series image - Reference only

Documents:

- 3D Model
- Drawing (PDF)
- Product Specification PS-70058-001 (PDF)
- Product Specification PS-70400-001 (PDF)
- Product Specification TS-70058-001-001 (PDF)
- Product Specification TS-70541-001-001 (PDF)
- RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	70450
Application	Signal, Wire-to-Board
Comments	Version F
Overview	SL™ Modular Connectors
Product Name	SL™
UPC	800754397902

Physical

Breakaway	No
Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Polyester
Net Weight	0.744/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Engineering Number	704500252

Reference - Drawing Numbers

Product Specification	PS-70058-001, PS-70400-001, TS-70058-001-001, TS-70541-001-001
Sales Drawing	SD-70450-0250-0275

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free Status
Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
70450 Series

Mates With
2.54mm Pitch C-Grid® Header 70229 , 70280 , 70246 , 70247

Use With
70058 , 71851

This document was generated on 07/31/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION