

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0877604216**  
**Status:** **Active**  
**Overview:** Milli-Grid™ Connector System  
**Description:** 2.00mm Pitch Milli-Grid™ Header, Right Angle, Through Hole, 42 Circuits, 0.38µm Gold (Au) Selective Plating, Tray, Lead-Free

**Documents:**

[3D Model](#) [Product Specification PS-87761-100 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**


CSA LR19980  
 UL E29179

**General**

Product Family PCB Headers  
 Series 87760  
 Application Board-to-Board, Signal, Wire-to-Board  
 Comments Lead-Free version of 87049 series  
 Overview Milli-Grid™ Connector System  
 Product Name Milli-Grid™  
 UPC 822348358731

**Physical**

Breakaway No  
 Circuits (Loaded) 42  
 Circuits (maximum) 42  
 Color - Resin Black  
 First Mate / Last Break No  
 Flammability 94V-0  
 Glow-Wire Compliant No  
 Guide to Mating Part No  
 Keying to Mating Part None  
 Lock to Mating Part None  
 Mated Height 4.00mm  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Gold  
 Material - Plating Termination Tin  
 Material - Resin High Temperature Thermoplastic  
 Net Weight 1.335/g  
 Number of Rows 2  
 Orientation Right Angle  
 PC Tail Length 2.60mm  
 PCB Locator No  
 PCB Retention None  
 PCB Thickness - Recommended 1.60mm  
 Packaging Type Tray  
 Pitch - Mating Interface 2.00mm  
 Pitch - Termination Interface 2.00mm  
 Plating min - Mating 0.381µm  
 Plating min - Termination 1.905µm  
 Polarized to Mating Part No  
 Polarized to PCB No  
 Shrouded No  
 Stackable Yes  
 Surface Mount Compatible (SMC) Yes  
 Temperature Range - Operating -55°C to +105°C



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per  
 -ED/01/2017 (12  
 January 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS Green Image  
 ELV Not Relevant  
 RoHS Phthalates Not Contained

**Search Parts in this Series**

87760 Series

**Mates With**

Milli-Grid™ Vertical Through Hole  
 Receptacle 79107 , 78787 , Milli-Grid™  
 Flex-to-Board Vertical Receptacle 79108  
 , Milli-Grid™ Vertical Surface Mount  
 Receptacle 79109 , 78788 , Milli-Grid™ Top  
 Entry Surface Mount Receptacle 87381

Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 2.0A

Voltage - Maximum 125V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 014

Lead-freeProcess Capability WAVE

Max. Cycles at Max. Process Temperature 001

Process Temperature max. C 265

**Material Info**

**Reference - Drawing Numbers**

Product Specification PS-87761-100

Sales Drawing SD-87760-109

This document was generated on 07/24/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**