

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192030183**
Status: **Active**
Overview: Splices
Description: Krimptite™ Temp-Term Butt Splice for 10-12 AWG Wire, 343°C (650° F), Loose Piece

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Splices
Series	<u>19203</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<u>Splices</u>
Product Name	Krimptite™
UPC	800755060096

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel
Net Weight	2.456/g
Packaging Type	Bag
Temperature Range - Operating	483°C
Wire Insulation Diameter	5.80mm
Wire Size AWG	10, 12

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	C-T-346
--------------------	---------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19203-012



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Reviewed

Search Parts in this Series

[19203 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION