

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0982680821](#)  
**Status:** **Active**  
**Overview:** Premo-Flex™ Cable Jumpers  
**Description:** 1.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 13 Circuits, 0.152m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-98268-001-001 (PDF)</a>
<a href="#">Product Specification PS-98268-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Cable
Series	<a href="#">98268</a>
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	<a href="#">Premo-Flex™ Cable Jumpers</a>
Product Name	Premo-Flex™FFC Jumper
UPC	800756944388

**Physical**

Cable Length	0.152m
Circuits (Loaded)	13
Circuits (maximum)	13
Packaging Type	Bag
Pitch - Termination Interface	1.25mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable


**Electrical**

Current - Maximum per Contact	1.4A
Voltage - Maximum	60V AC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-98268-001-001
Product Specification	PS-98268-001-001
Sales Drawing	SD-98268-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[98268](#) Series

**Use With**

<a href="http://www.molex.com/product/ffc">Molex FFC – FPC connector</a>. Be sure to match like plating.