

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194290039](#)
Status: **Active**
Overview: MX150L™ Industrial Sealed Connector System
Description: MX150L™ 12 Circuit Panel Mount Plug for 14-22 AWG Wire, Rear Mount Flange Assembly, with Gasket

Documents:

3D Model	Packaging Specification PK-19429-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19417-001-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Housings
Series	<u>19429</u>
Application	Power, Wire-to-Wire
Comments	For Inside Panel Mount Application. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	<u>MX150L™ Industrial Sealed Connector System</u>
Product Literature Order No	987650-2181
Product Name	MX150L™
UPC	822348613281

Physical

Circuits (maximum)	12
Gender	Plug
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Net Weight	22.249/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	18.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19429-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19429-007



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Reviewed

Search Parts in this Series

19429 Series

Mates With

19418 MX150L™ Receptacle Assemblies

Use With

19417 MX150L™ Male Crimp Terminals