

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0393710004

Status:

Active

Overview:

Eurostyle™ Terminal Blocks

Description:

7.50mm Beau Eurostyle Pluggable PCB Terminal Block, 180° Wire Entry, 4 Circuits

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification

UL

E48521

General

Product Family

Terminal Blocks

Series

39371

Application

N/A

Component Type

Plug

Overview

Eurostyle™ Terminal Blocks

Product Name

Eurostyle™ Pluggable

Type

Euro Block

UPC

822348040186

Physical

Circuits (Loaded)

4

Entry Angle

180° Angle

Flammability

94V-0

Lock to Mating Part

None

Number of Rows

1

Orientation

Right Angle

PCB Retention

N/A

Panel Mount

No

Pitch - Mating Interface

7.50mm

Pitch - Termination Interface

7.50mm

Polarized to Mating Part

Yes

Stackable

Yes

Temperature Range - Operating

110°C

Wire Size AWG

12, 14, 16, 18, 20, 22, 24, 26, 28, 30

Wire Size mm²

0.05-2.50

Electrical

Current - Maximum per Contact

15.0A

Voltage - Maximum

300V

Material Info

Engineering Number

MX-CIF04003-0N

Reference - Drawing Numbers

Sales Drawing

SD-39371-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

39371 Series

Mates With

39372 , 39373 Headers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION