
This document was generated on 08/01/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0191410021
Status: Active
Overview: Solderless Terminals
Description: Krimptite™ Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier



Series image - Reference only

Documents:

Drawing (PDF)
Product Specification PS-19902-011-001 (PDF)
Product Specification PS-19902-015-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19141
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Solderless Terminals
Product Name	Krimptite™
Type	Spade
UPC	800753103191

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.549/g
Packaging Type	Adhesive Tape on Reel
Stud Size	6 (M3.5)
Wire Size AWG	18, 20, 22
Wire Size mm²	0.25-1.50

Electrical

Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Engineering Number	AA-135-06T

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-015-001
Sales Drawing	AACD10303

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
19141 Series

This document was generated on 08/01/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION