

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0431784002**  
**Status:** **Active**  
**Overview:** Sabre™ Power Connector  
**Description:** Sabre™ Crimp Terminal, Male, 18-20 AWG, 3.30mm max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-44441-9999-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	43178
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Sabre™ Power Connector</a>
Product Literature Order No	987650-5662
Product Name	Sabre™
UPC	884982063945

**Physical**

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.550/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.30mm max.
Wire Size AWG	18, 20
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-44441-9999-001
Sales Drawing	SD-43178-002



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[43178 Series](#)

**Mates With**

[43375 Female Crimp Terminals](#)

**Use With**

[43680 Plug Housings](#)