

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0705530007

Status:

Active

Overview:

SL™ Modular Connectors

Description:

2.54mm Pitch SL™ Header, Low Profile, Single Row, Right Angle, 3.05mm Pocket, Shrouded, 8 Circuits, 0.38µm Gold (Au) Selective Plating, Tin (Sn) PC Tail Plating



Series image - Reference only

- Documents:
- 3D Model

Drawing (PDF)

Product Specification PS-70400-001 (PDF)

Product Specification PS-70541-001 (PDF)

Product Specification TS-70541-001-001 (PDF)

Product Specification TS-70541-100-001 (PDF)

Packaging Specification PK-70873-0015 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

70553

Application

Signal, Wire-to-Board

Overview

SL™ Modular Connectors

Product Name

SL™

UPC

800753597419

Physical

Breakaway

No

Circuits (Loaded)

8

Circuits (maximum)

8

Color - Resin

Black

Durability (mating cycles max)

50

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

Yes

Lock to Mating Part

Yes

Material - Metal

Brass, Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

1.697/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.30mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Tube

Pitch - Mating Interface

2.54mm

Plating min - Mating

0.381µm

Plating min - Termination

1.905µm

Polarized to Mating Part

Yes

Shrouded

Fully

Stackable

No

Temperature Range - Operating

-40°C to +105°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

3.0A

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

70553 Series

Mates With

SL™ Crimp Housing 70066 Option N, 70066
Option G, 70430 Option G, 70400 Option G

Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	003
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-70873-0015
Product Specification	PS-70400-001, PS-70541-001, TS-70541-001-001, TS-70541-100-001
Sales Drawing	SDA-70553-****

This document was generated on 07/24/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION