

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192020055](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** NylaKrimp™ Butt Splice for 6 AWG Wire

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification PS-19902-011-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Splices
Series	<a href="#">19202</a>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<a href="#">Splices</a>
Product Name	Butt, NylaKrimp™
UPC	800753048324

**Physical**

Barrel Type	Closed - Brazed
Color - Resin	Blue
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	9.150/g
Packaging Type	Bag
Temperature Range - Operating	-55°C to +105°C
Wire Insulation Diameter	8.76mm max.
Wire Size AWG	6

**Electrical**


Voltage - Maximum	300V
-------------------	------

**Material Info**

Engineering Number	E-762
--------------------	-------

**Reference - Drawing Numbers**

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19202-003



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19202](#) Series