This document was generated on 08/15/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0191540048
Status: Active
Overview: Splices
Description: InsulKrimp™ Butt Splice for 4 AWG Wire



Series image - Reference only

Documents:

Drawing (PDF)
Product Specification PS-19902-011-001 (PDF)
Product Specification PS-19902-013-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	19154
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	Butt, InsulKrimp™
UPC	800753109117

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-0
Insulation	PVC
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	3.985/g
Packaging Type	Bag
Wire Insulation Diameter	13.10mm max.
Wire Size AWG	4

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Engineering Number	F-664X

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19154-004

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free Status
Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
19154 Series

This document was generated on 08/15/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION