

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0469990101
Status: Active
Overview: KK® Interconnect System - Molex
Description: KK® High Pressure Crimp Terminal 7879, 24-30 AWG, Bag Tin (Sn)

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-7879-001 \(PDF\)](#)

General
Product Family Crimp Terminals
Series 7879
Application Signal
Crimp Quality Equipment Yes
Overview KK® Interconnect System - Molex
Packaging Alternative 50-29-1900 (Reel)
Product Name KK® High Pressure
UPC 884982607262

Physical
Gender Female
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Nickel
Net Weight 0.118/g
Packaging Type Bag
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.57mm max.
Wire Size AWG 22, 24, 26, 28, 30
Wire Size mm² N/A

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number 7879-1(P154)L

Reference - Drawing Numbers
Product Specification PS-7879-001
Sales Drawing SD-7879



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/30/2017 (7 July 2017) Halogen-Free Status Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS Green Image ELV Not Relevant RoHS Phthalates Not Contained
--	--

Search Parts in this Series
[7879 Series](#)