

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192030005](#)
Status: **Active**
Overview: [High-Temperature Temp Terms Terminals and Splices](#)
Description: Krimptite™ Temp-Term Ring Tongue Terminal for 18 to 22 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier

Documents:

Drawing (PDF)	Product Specification PS-19902-015-001 (PDF)
Product Specification PS-19902-011-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E32244

General

Product Family	Ring and Spade Terminals
Series	19203
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite™, Temp-Terms
Type	Ring
UPC	800753049369

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Nickel
Net Weight	0.804/g
Packaging Type	Adhesive Tape on Reel
Stud Size	1/4" (M6)
Wire Size AWG	18, 20, 22
Wire Size mm²	0.25-1.50

Material Info

Engineering Number A-S-122-14T

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-015-001
Sales Drawing	SD-19203-036



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19203 Series](#)