

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009483125](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 396 PC Board Connector, Right Angle, Polyester Connector, Gold \(Au\) Selective, 12 Circuits](#)

Documents:

3D Model	Product Specification PS-08-50-001 (PDF)
Drawing (PDF)	Packaging Specification PK-41815-001-000 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	41815
Application	Board-to-Board, Power
Overview	KK® Interconnect System - Molex
Product Name	KK® 396
UPC	800754254069

Physical


Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Natural
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	3.892/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.68mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	0.80mm
Packaging Type	Tray
Pitch - Mating Interface	3.96mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to PCB	Yes
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[41815](#) Series

Mates With

[KK® 396 Header 41771](#) , [41772](#) , [41791](#) , [41792](#) , [42491](#) , [42492](#) , [42891](#) , [41661](#) , [41662](#) , [41671](#) , [41672](#) , [41681](#)

Material Info

Engineering Number

A-41815-0435

Reference - Drawing Numbers

Packaging Specification

PK-41815-001-000

Product Specification

PS-08-50-001

Sales Drawing

SDA-41815-000, SDA-41815-002

This document was generated on 08/22/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION