


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0908160214**
Status: **Active**
Overview: Picoflex® Ribbon-Cable Connectors
Description: Picoflex® Surface Mount Latched Vertical Header with PCB Pegs, 14 Circuits, Tin (Sn) Plating, Black

Documents:

3D Model	Packaging Specification PK-90816-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-90816-006 (PDF)
Product Specification PS-99020-0011 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification TS-90816-001-001 (PDF)	



General

Product Family	PCB Headers
Series	90816
Application	Signal, Wire-to-Board
Overview	Picoflex® Ribbon-Cable Connectors
Product Name	Picoflex®
UPC	883906444327

Physical

Breakaway	No
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	5
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	Nylon
Net Weight	0.842/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	1.05mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.076µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	250V

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

90816 Series

Mates With

90327 Picoflex® PF-50

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-90816-001-001, PK-90816-006

PS-99020-0011, TS-90816-001-001

SD-90816-001

This document was generated on 07/26/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION