

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0393570008](#)
Status: **Active**
Overview: Eurostyle™ Terminal Blocks
Description: 3.50mm Pitch Beau Eurostyle™ Fixed Mount PCB Terminal Block, 8 Circuits

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E48521

General

Product Family Terminal Blocks
 Series [39357](#)
 Application N/A
 Component Type One Piece
 Overview [Eurostyle™ Terminal Blocks](#)
 Product Name Eurostyle™ Fixed Mount
 Type Euro Block
 UPC 756054634189

Physical

Circuits (Loaded) 8
 Circuits (maximum) 8
 Entry Angle Horizontal
 Flammability 94V-0
 Lock to Mating Part None
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 3.50mm
 PCB Retention None
 PCB Thickness - Recommended 1.60mm
 Panel Mount No
 Pitch - Mating Interface 3.50mm
 Pitch - Termination Interface 3.50mm
 Polarized to Mating Part No
 Shrouded Fully
 Stackable Yes
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -30°C to +85°C
 Wire Size AWG 16, 18, 20, 22, 24, 26, 28
 Wire Size mm² 0.20-1.00

Electrical

Current - Maximum per Contact 17.5A
 Voltage - Maximum 300V

Solder Process Data


Lead-free Process Capability WAVE
 Max. Cycles at Max. Process Temperature 005
 Process Temperature max. C 260

Material Info

Engineering Number MX-MTB08008-0N

Reference - Drawing Numbers

Sales Drawing SD-39357-001



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[39357 Series](#)

This document was generated on 07/10/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION