

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191540015**
Status: **Active**
Overview: Splices
Description: InsulKrimp™ Butt Splice for 14-16 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-007-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Splices
 Series 19154
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 MolexKits Yes
 Overview Splices
 Product Name Butt, InsulKrimp™
 UPC 800753108837

Physical

Barrel Type Closed
 Color - Resin Blue
 Flammability 94V-0
 Insulation PVC
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin PVC
 Net Weight 1.435/g
 Packaging Type Bag
 Temperature Range - Operating -40°C to +105°C
 Wire Insulation Diameter 4.45mm max.
 Wire Size AWG 14, 16
 Wire Size mm² 1.30-2.00

Electrical

Voltage - Maximum 600V

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number B-231X

Reference - Drawing Numbers

Product Specification PS-19902-007-001, PS-19902-011-001,
 PS-19902-013-001
 Sales Drawing SD-19154-006



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/30/2017 (7 July
 2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19154 Series