

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192030052](#)  
**Status:** **Active**  
**Overview:** [High-Temperature Temp Terms Terminals and Splices](#)  
**Description:** Krimptite™ Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-015-001 (PDF)</a>
<a href="#">Product Specification PS-19902-011-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

UL E32244

**General**

Product Family	Ring and Spade Terminals
Series	<a href="#">19203</a>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<a href="#">High-Temperature Temp Terms Terminals and Splices</a>
Product Name	Krimptite™, Temp-Terms
Type	Ring
UPC	800753049734

**Physical**

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.658/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Size AWG	14, 16
Wire Size mm²	1.00-2.50

**Material Info**

Engineering Number B-S-137-10T

**Reference - Drawing Numbers**

Product Specification	PS-19902-011-001, PS-19902-015-001
Sales Drawing	SD-19203-017



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19203 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**