

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [87438-1243](#)  
**Status:** **Active**  
**Overview:** Pico-SPOX™ Wire-to-Board Connector System  
**Description:** 1.50mm Pitch Pico-SPOX™ Wire-to-Board Header, Surface Mount, Right Angle, Shrouded, 12 Circuits, Embossed Tape on Reel, Beige

**Documents:**

[3D Model](#) [Packaging Specification SPK-87438-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-87437-001 \(PDF\)](#)

**Agency Certification**

UL E29179

**General**


Product Family PCB Headers  
 Series [87438](#)  
 Application Signal, Wire-to-Board  
 Overview Pico-SPOX™ Wire-to-Board Connector System  
 Product Name Pico-SPOX™  
 UPC 822348439072

**Physical**

Breakaway No  
 Circuits (Loaded) 12  
 Circuits (maximum) 12  
 Color - Resin Beige  
 Durability (mating cycles max) 10  
 First Mate / Last Break No  
 Flammability 94V-0  
 Glow-Wire Compliant No  
 Guide to Mating Part No  
 Keying to Mating Part Yes  
 Lock to Mating Part Yes  
 Material - Metal Brass  
 Material - Plating Mating Tin over Nickel  
 Material - Plating Termination Tin over Nickel  
 Material - Resin High Temperature Thermoplastic  
 Net Weight 0.613/g  
 Number of Rows 1  
 Orientation Right Angle  
 PCB Locator No  
 PCB Retention None  
 Packaging Type Embossed Tape on Reel  
 Pitch - Mating Interface 1.50mm  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Polarized to Mating Part Yes  
 Polarized to PCB No  
 Shrouded Fully  
 Stackable No  
 Temperature Range - Operating -55°C to +105°C  
 Termination Interface: Style Surface Mount

**Electrical**

Current - Maximum per Contact 2.5A



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[87438Series](#)

**Mates With**

[87439 Pico-SPOX™ Wire-to-Board Housing](#)

Voltage - Maximum

250V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification

SPK-87438-001

Product Specification

PS-87437-001, RPS-87437, RPS-87437-001,

RPS-87437-200

Sales Drawing

SD-87438-001

This document was generated on 04/23/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**