

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0191540049
Status: Active
Overview: Splices
Description: InsulKrimp™ Butt Splice for 2 AWG Wire

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E32244

General
Product Family Splices
Series 19154
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Splices
Product Name Butt, InsulKrimp™
UPC 800753109131

Physical
Barrel Type Closed
Color - Resin Red
Flammability 94V-0
Insulation PVC
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin PVC
Net Weight 22.727/g
Packaging Type Bag
Wire Insulation Diameter 16.50mm max.
Wire Size AWG 2

Material Info
Engineering Number G-672X

Reference - Drawing Numbers
Product Specification PS-19902-011-001, PS-19902-013-001
Sales Drawing SD-19154-004



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
ED/108/2014 (17 Dec
2014)
Halogen-Free
Status
Not Low-Halogen
**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Reviewed

Search Parts in this Series
[19154 Series](#)