

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0191600083
Status: Active
Overview: Splices
Description: Closed-End Insulated Splice for 10-16 AWG Wire, Tape and Reel

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-015-001 \(PDF\)](#)
[Packaging Specification PK-19408-109-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E32244

General
Product Family Splices
Series 19160
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Splices
Product Name Closed-End Insulated
UPC 800753110922

Physical
Barrel Type Closed
Color - Resin Natural
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 1.030/g
Packaging Type Adhesive Tape on Reel
Temperature Range - Operating 105°C
Wire Insulation Diameter 9.65mm max.
Wire Size AWG 10, 12, 14, 16

Electrical
Voltage - Maximum 600V

Material Info
Engineering Number NC-1610T

Reference - Drawing Numbers
Packaging Specification PK-19408-109-001
Product Specification PS-19902-015-001
Sales Drawing SD-19160-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
ED/30/2017 (7 July
2017)
Halogen-Free
Status
Low-Halogen
**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19160 Series](#)