

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190690225](#)  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** Krimptite™ Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 5/16" (M8), Length 24.18mm, Mylar Tape Carrier

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19069](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Solderless Terminals](#)  
 Product Name Krimptite™  
 Type Ring  
 UPC 800753068193

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.791/g  
 Packaging Type Adhesive Tape on Reel  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Stud Size 5/16" (M8)  
 Termination Interface: Style Crimp or Compression  
 Wire Size AWG 10, 12  
 Wire Size mm² 4.00-6.00

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Engineering Number C-130-56T

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-015-001  
 Sales Drawing CCD10101



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/30/2017 (7 July  
 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[19069 Series](#)