

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002067103**
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket PC Tail Terminal, Series 1779, Female, with 2.54µm Tin (Sn) Plated Brass Contact, Bag Packaged

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-1190-003 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	<u>1779</u>
Application	Power
Comments	PC Tail Brass for Standard .062" Housing
Crimp Quality Equipment	Yes
Overview	<u>Standard .062" Pin and Socket Power Connectors</u>
Product Name	Standard .062"
UPC	800753618404

Physical


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.160/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.00mm max.
Wire Size AWG	N/A
Wire Size mm ²	N/A

Material Info

Engineering Number	1779-(P909)L
--------------------	--------------

Reference - Drawing Numbers

Packaging Specification	PK-1190-003
Sales Drawing	SD-1779-*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

1779 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Extraction Tool	<u>0011030002</u>