

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192110006](#)
Status: **Active**
Overview: [Wire Pins](#)
Description: Krimptite™ Wire Pin Terminal for 16-14 AWG Wire, Mylar Tape Carrier

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Crimp Terminals
 Series [19211](#)
 Application Power
 Comments Pin Length 9.65mm
 Crimp Quality Equipment Yes
 Overview [Wire Pins](#)
 Packaging Alternative [19211-0005](#) (Loose)
 Product Name Wire Pin
 UPC 800753053229

Physical


Gender Male
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.626/g
 Packaging Type Adhesive Tape on Reel
 Plating min - Mating 0.762µm
 Plating min - Termination 0.762µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 2.26mm max.
 Wire Size AWG 14, 16

Material Info

Engineering Number WP-1614T

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-015-001
 Sales Drawing SD-19211-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[19211](#) Series