
This document was generated on 08/22/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0510650700

Status: Active

Description: 2.00mm Pitch Micro-Latch™ Wire-to-Board Housing, Friction Lock, 7 Circuits



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Product Specification 510650000-000 (PDF)
Product Specification PS-51065-005 (PDF)
Product Specification PS-51065-016-001 (PDF)
Product Specification PS-51065-017-001 (PDF)
Product Specification PS-51065-018-001 (PDF)
Packaging Specification SPK-51065-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	51065
Application	Signal, Wire-to-Board
Product Name	Micro-Latch™
UPC	800753574281
Physical	
Circuits (maximum)	7
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Polyester
Net Weight	182.600/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Material Info	
Reference - Drawing Numbers	
Packaging Specification	SPK-51065-001-001
Product Specification	510650000-000, PS-51065-005, PS-51065-016-001, PS-51065-017-001, PS-51065-018-001
Sales Drawing	SD-51065-004, SD-51065-006

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free Status
Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
51065 Series

Mates With
53253 PCB Header, 53254 PCB Header

Use With
50212 Crimp Terminal

This document was generated on 08/22/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION