

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0191600024
Status: Active
Overview: Splices
Description: Closed-End Insulated Splice for 8 AWG Wire

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-013-001 \(PDF\)](#)
[Packaging Specification PK-19408-109-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19160
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	Closed-End Insulated
UPC	800753110298
Physical	
Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.230/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	12.19mm max.
Wire Size AWG	8
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	NC-8
Reference - Drawing Numbers	
Packaging Specification	PK-19408-109-001
Product Specification	PS-19902-013-001
Sales Drawing	SD-19160-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/30/2017 (7 July 2017) Halogen-Free Status Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[19160 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION