

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5022250801](#)  
**Status:** **Active**  
**Overview:** CMC and CMX Sealed, Hybrid, Modular Connectors  
**Description:** 2.50mm, 3.50mm, 3.70mm CMC Header, Right Angle, 80 Circuits

**Documents:**

[3D Model](#) [Product Specification PS-64319-001-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	PCB Headers
Series	<a href="#">502225</a>
Application	Power, Wire-to-Board
Comments	Coding: 32w Black, 48w Brown
Overview	<a href="#">CMC and CMX Sealed, Hybrid, Modular Connectors</a>
Product Name	CMC
UPC	822350659871

**Physical**

Breakaway	No
Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Black
Durability (mating cycles max)	20
First Mate / Last Break	Yes
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	59400.000/mg
Number of Rows	4
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.50mm, 3.50mm, 3.70mm
Pitch - Termination Interface	2.50mm, 3.50mm, 3.70mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Solder or Weld

**Electrical**

Current - Maximum per Contact	6.0A
Voltage - Maximum	14V DC

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	025
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001



**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[502225](#) Series

**Mates With**

[64319-3211](#) CMC Connector, [64320-1319](#)  
CMC Connector

**Use With**

[64319-3211](#) CMC Connector, [64320-1319](#)  
CMC Connector, [64322](#) Terminal,  
[64323](#) Terminal, [64320-1301](#) Wire Cap,  
[64319-1201](#) Wire Cap, [64325](#) Blind Plug

Process Temperature max. C 260

**Material Info**

**Reference - Drawing Numbers**

Product Specification PS-64319-001-001  
Sales Drawing SD-502225-001

This document was generated on 08/03/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**